

PNA - Product Notification Alert

Split Rubber Compression Ring

Product Range:	AES/ PES, AS/ PS and AL/ PL
Product Stock Code:	
Release Date:	26 th March 2025

Feature:

AusProof's new design for the Compression Rubber across all of the low voltage range is now split, making it easier to replace the existing rubber without disrupting any terminations.


This change has been thoroughly tested and approved by AusProof's certifying body, Simtars. The **Certificate of Conformity** (ANZEx 16.2005X, Issue No. 7) is now available for access on our website. You can view the certificate directly at the following link: www.ausproof.com.au



The ends of the split compression ring should meet closely and evenly, without gaps or overlap, to ensure a proper seal.



For the PS 150 amp, 50-60 mm glands only, an updated pressure washer was necessary to implement these design changes. To replace the Solid Compression Ring with the updated Split Rubber Compression Ring, a new termination, along with the updated pressure washer is required, as needed. This is a one-time adjustment. Once the new Pressure Washer (PN. 10397) is installed, the Split Rubber Compression Ring can be easily replaced in the future.



The new 50mm–60mm pressure washer has been clearly marked to indicate that it is a new component, and therefore does not need to be replaced.